



Material	81000.260
Material description	Ammonium hydrogen difluoride
Grade	AnalaR NORMAPUR
CAS Number	1341-49-7
Molecular formula	H5F2N
Molecular mass	57.04

Characteristics	Specifications
Assay	Min. 98.5 %
Heavy metals (as Pb)	Max. 0.03 %
Ignition residue (SO ₄)	Max. 0.02 %
Insolubility in water	Max. 50 ppm
Cl (Chloride)	Max. 5 ppm
SO ₄ (Sulphate)	Max. 50 ppm
Ca (Calcium)	Max. 10 ppm
Fe (Iron)	Max. 80 ppm

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Anja Vanhalle, Head of Laboratory - Haasrode
VWR International bvba; Geldenaaksebaan 464; BE-3001
Leuven; Belgium

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.