

Material	20066.321
Material description	Acetone
Grade	AnalaR NORMAPUR Reag. Ph.Eur., Reag. USP, ACS
CAS Number	67-64-1
Molecular formula	CH ₃ COCH ₃
Molecular mass	58.08

Characteristics	Specifications
Assay (on anhydrous substance)	Min. 99.8 %
Appearance of solution	Passes test Ph.Eur.
Aqueous solution	Passes test
Identification B	Passes test Ph.Eur.
Identification C	Passes test Ph.Eur.
Insolubility in water	Passes test
IR Spectrum	Passes test
Related substances	Passes test Ph.Eur.
Acidity	Max. 0.0003 meq/g
Alkalinity	Max. 0.0003 meq/g
Boiling point	55.3 --> 56.9 °C
Colouration	Max. 10 APHA
Density (20/4)	0.790 --> 0.792
Density (20/20)	0.790 --> 0.793
Aldehydes (as HCHO)	Max. 10 ppm
Ethanol	Max. 100 ppm
Evaporation residue	Max. 5 ppm
Methanol	Max. 0.05 %
2-Propanol	Max. 100 ppm
Substances reducing KMnO ₄ (as O)	Max. 2 ppm
Water	Max. 0.2 %
PO ₄ (Phosphate)	Max. 100 ppb
Al (Aluminium)	Max. 0.1 ppm
B (Boron)	Max. 0.02 ppm
Ba (Barium)	Max. 0.05 ppm
Ca (Calcium)	Max. 0.5 ppm
Cd (Cadmium)	Max. 0.01 ppm
Co (Cobalt)	Max. 0.01 ppm

>>> Continued on page 2 >>>



Characteristics	Specifications
Cr (Chromium)	Max. 0.02 ppm
Cu (Copper)	Max. 0.01 ppm
Fe (Iron)	Max. 0.05 ppm
K (Potassium)	Max. 0.1 ppm
Mg (Magnesium)	Max. 0.05 ppm
Mn (Manganese)	Max. 0.01 ppm
Na (Sodium)	Max. 0.5 ppm
Ni (Nickel)	Max. 0.01 ppm
Pb (Lead)	Max. 0.01 ppm
Sn (Tin)	Max. 0.1 ppm
Sr (Strontium)	Max. 0.02 ppm
Zn (Zinc)	Max. 0.01 ppm
Conforms to ACS	Passes test
Conforms to Reag. Ph.Eur.	Passes test
Conforms to Reag. USP	Passes test

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;
France

