

# Safety Data Sheet

Revision date: 29.08.2022

Version: 7.2

Print date: 29.08.2022

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

Trade name/designation:	Phosphomolybdotungstic Reagent Dilute Reag. Ph. Eur. 1065001
Product No.:	87894
CAS No.:	not applicable
Other means of identification:	none

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses:	General chemical reagent
---------------------------	--------------------------

### 1.3 Details of the supplier of the safety data sheet

*Singapore*

#### **VWR Singapore Pte Ltd.**

Street	18 Gul Drive
Postal code/City	Singapore 629468
Telephone	+65 6505 0760
Telefax	+65 6264 3780
E-mail (competent person)	SDS@avantorsciences.com

### 1.4 Emergency phone number

Telephone	+65 (0) 6505 0760 (office hours: 8 am-5 pm)
-----------	---

## SECTION 2: Hazard identification

### 2.1 Classification of the substance or mixture

Hazard classes and hazard categories	Hazard statements
Substance or mixture corrosive to metals, category 1	H290

### 2.2 Label elements

#### Hazard pictograms



**Signal word:** Warning

Hazard statements	
H290	May be corrosive to metals.

Precautionary statements	
P234	Keep only in original container.
P390	Absorb spillage to prevent material damage.
P406	Store in a corrosive resistant/... container with a resistant inner liner.

### 2.3 Other hazards

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

## SECTION 3: Composition / information on ingredients

### 3.1 Substances

not applicable

### 3.2 Mixtures

#### Composition / Information on ingredients

Substance name	Concentration	Identifier	Hazard classes and hazard categories
Sodium wolframate dihydrate	2 - 5%	CAS No.: 10213-10-2	Acute Tox. 4 - H302
Hydrochloric acid	1 - 3%	CAS No.: 7647-01-0	Met. Corr. 1 - H290 Skin Corr. 1B - H314 STOT SE 3 - H335
Orthophosphoric acid	1 - 3%	CAS No.: 7664-38-2	Met. Corr. 1 - H290 Acute Tox. 4 - H302 Skin Corr. 1B - H314 Eye Dam. 1 - H318
Lithium sulphate monohydrate	5 - 10%	CAS No.: 10102-25-7	Acute Tox. 4 - H302

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

#### General information

When in doubt or if symptoms are observed, get medical advice. If unconscious but breathing normally, place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

#### After inhalation

Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration. In case of respiratory tract irritation, consult a physician.

#### In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

#### After eye contact:

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

#### In case of ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

#### Self-protection of the first aider

First aider: Pay attention to self-protection!

### 4.2 Most important symptoms and effects, both acute and delayed

no data available

### 4.3 Indication of any immediate medical attention and special treatment needed

no data available

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### **Suitable extinguishing media**

The product itself does not burn.

Co-ordinate fire-fighting measures to the fire surroundings.

#### **Extinguishing media which must not be used for safety reasons**

no restriction

### 5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated:

Pyrolysis products, toxic

### 5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives.

Special protective equipment for firefighters:

Wear a self-contained breathing apparatus and chemical protective clothing.

#### **Additional information**

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use water spray jet to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety.

### 6.2 Environmental precautions

Discharge into the environment must be avoided.

### 6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Collect in closed and suitable containers for disposal.

### 6.4 Additional information

Clear spills immediately.

## SECTION 7: Handling and storage

### 7.1 Precautions for safe handling

All work processes must always be designed so that the following is as low as possible:

Inhalation

skin contact

Eye contact

Use extractor hood (laboratory).

If handled uncovered, arrangements with local exhaust ventilation have to be used.

If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

### 7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: no data available

Storage class: no data available

Keep container tightly closed and in a well-ventilated place. Keep/Store only in original container.

### 7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

### 8.2 Exposure controls

#### 8.2.1 Appropriate engineering controls

no data available

#### 8.2.2 Personal protection equipment

no data available

*Eye/face protection*

no data available

Recommendation: no data available

*Skin protection*

no data available

By short-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,12 mm
Breakthrough time::	> 480 min
Recommended glove articles:	VWR 112-0998

By long-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,38 mm
Breakthrough time::	> 480 min
Recommended glove articles:	VWR 112-1381

*Respiratory protection*

no data available

Suitable respiratory protection apparatus:	no data available
Recommendation:	no data available
Suitable material:	no data available
Recommendation:	no data available

*Additional information*

no data available

**8.2.3** *Environmental exposure controls*  
no data available

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	liquid
Colour:	no data available
(b) Odour:	no data available
(c) Odour threshold:	no data available

#### Safety relevant basic data

(d) pH:	no data available
(e) Melting point/freezing point:	no data available
(f) Initial boiling point and boiling range:	no data available
(g) Flash point:	no data available
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	not applicable
(j) Flammability or explosive limits	
Lower explosion limit:	no data available
Upper explosion limit:	no data available
(k) Vapour pressure:	no data available
(l) Vapour density:	no data available
(m) Density:	no data available
(n) Solubility(ies)	
Water solubility:	no data available
(o) Partition coefficient: n-octanol/water:	no data available
(p) Auto-ignition temperature:	no data available
(q) Decomposition temperature:	not applicable
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	no data available
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable
(u) Particle characteristics:	does not apply to liquids

### 9.2 Other information

Bulk density:	no data available
Refraction index:	no data available
Dissociation constant:	no data available
Surface tension:	no data available
Henry's Law Constant:	no data available

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

## 10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

## 10.3 Possibility of hazardous reactions

no data available

## 10.4 Conditions to avoid

no data available

## 10.5 Incompatible materials

no data available

## 10.6 Hazardous decomposition products

no data available

## 10.7 Additional information

no data available

# SECTION 11: Toxicological information

## 11.1 Information on toxicological effects

### Acute effects

#### *Acute oral toxicity:*

Sodium wolframate dihydrate - LD50: > 1190 mg/kg - Rat - (RTECS)

Orthophosphoric acid - LD50: 300 - 2000 mg/kg - Rat - (OECD 423)

Lithium sulphate monohydrate - LD50: > 613 mg/kg - Rat - (Merck KGaA)

#### *Acute dermal toxicity:*

Sodium wolframate dihydrate - LD50: 2000 mg/kg - Rat - (IUCLID)

Hydrochloric acid - LD50: > 5010 mg/kg - Rabbit - (Japan GHS Basis for Classification Data)

Lithium sulphate monohydrate - LD50: 3000 mg/kg - Rabbit - (IUCLID)

#### *Acute inhalation toxicity:*

Sodium wolframate dihydrate - LC50: 5.01 mg/m<sup>3</sup> - Rat - (IUCLID)

Hydrochloric acid - LC50: 8.3 mg/l (30 min) - Rat - (IUCLID)

Hydrochloric acid - LC50: 45.6 mg/l (5 min) - Rat - (IUCLID)

Lithium sulphate monohydrate - LC50: 2000 mg/m<sup>3</sup> - Rat - (IUCLID)



**Irritant and corrosive effects**

*Primary irritation to the skin:*

not applicable

*Irritation to eyes:*

not applicable

*Irritation to respiratory tract:*

not applicable

**Respiratory or skin sensitisation**

In case of skin contact: not sensitising

After inhalation: not sensitising

**STOT-single exposure**

not applicable

**STOT-repeated exposure**

not applicable

**CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)****Carcinogenicity**

No indication of human carcinogenicity.

**Germ cell mutagenicity**

No indications of human germ cell mutagenicity exist.

**Reproductive toxicity**

No indications of human reproductive toxicity exist.

**Aspiration hazard**

not applicable

**Other adverse effects**

no data available

**Additional information**

no data available

## SECTION 12: Ecological information

### 12.1 Ecotoxicity

**Fish toxicity:**

no data available

**Daphnia toxicity:**

Hydrochloric acid - LC50: 250 mg/l (48 h) - Portmann, J.E., and K.W. Wilson 1971. The Toxicity of 140 Substances to the Brown Shrimp and Other Marine Animals. Shellfish Information Leaflet No.22 (2nd Ed.):12 p.

Hydrochloric acid - EC50: 0.45 (pH: 4.9) mg/l (48 h) Daphnia Magna - OECD 202

Orthophosphoric acid - EC50: 100 mg/l (48 h) Daphnia Magna - OECD 202

**Algae toxicity:**

Hydrochloric acid - EC50: 0.73 (pH: 4.7) mg/l (72 h) freshwater - OECD 201

Hydrochloric acid - NOEC: mg/l (72 h) freshwater - OECD 201

Orthophosphoric acid - EC10: 100 mg/l (72 h) *Desmodesmus subspicatus* - OECD 201

Orthophosphoric acid - EC50: 100 mg/l (72 h) *Desmodesmus subspicatus* - OECD 201

**Bacteria toxicity:**

Orthophosphoric acid - NOEC: 1000 mg/l (3 h) - OECD 209

**12.2 Persistence and degradability**

no data available

**12.3 Bioaccumulative potential**

Partition coefficient: n-octanol/water: no data available

**12.4 Mobility in soil:**

no data available

**12.5 Results of PBT/vPvB assessment**

not applicable

**12.6 Other adverse effects**

no data available

**SECTION 13: Disposal considerations****13.1 Waste treatment methods****Appropriate disposal / Product**

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

**Appropriate disposal / Package**

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

**Additional information**

no data available

## SECTION 14: Transport information

### Land transport (ADR/RID)

14.1	UN-No.:	3264
14.2	Proper Shipping Name:	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (HYDROCHLORIC ACID/PHOSPHORIC ACID SOLUTION)
14.3	Class(es):	8
	Classification code:	C1
	Hazard label(s):	8
14.4	Packing group:	III
14.5	Environmental hazards:	No
14.6	Special precautions for user:	
	Hazard identification number (Kemler No.):	80
	tunnel restriction code:	E
		(Passage forbidden through tunnels of category E.)

### Sea transport (IMDG)

14.1	UN-No.:	3264
14.2	Proper Shipping Name:	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (HYDROCHLORIC ACID/PHOSPHORIC ACID SOLUTION)
14.3	Class(es):	8
	Classification code:	
	Hazard label(s):	8
14.4	Packing group:	III
14.5	Environmental hazards:	No
	Marine pollutant:	No
14.6	Special precautions for user:	
	Segregation group:	1
	EmS-No.	F-A S-B
14.7	Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	
	not relevant	

### Air transport (ICAO-TI / IATA-DGR)

14.1	UN-No.:	3264
14.2	Proper Shipping Name:	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (HYDROCHLORIC ACID/PHOSPHORIC ACID SOLUTION)
14.3	Class(es):	8
	Classification code:	
	Hazard label(s):	8
14.4	Packing group:	III
14.5	Special precautions for user:	

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### National regulations

- Workplace Safety and Health Act
- Workplace Safety and Health (Permissible Exposure Levels of Toxic Substances) Order
- Environmental Protection and Management Act (EPMA) - Second Schedule, Part 1, Control of Hazardous Substances
- Maritime and Port Authority of Singapore (MPA) - Dangerous Goods, Petroleum and Explosives Regulations

## SECTION 16: Other information

#### Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists  
 ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road  
 AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)  
 CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures  
 DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)  
 DNEL - Derived No Effect Level  
 Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)  
 IATA-DGR - International Air Transport Association-Dangerous Goods Regulations  
 ICAO-TI - International Civil Aviation Organization-Technical Instructions  
 IMDG - International Maritime Code for Dangerous Goods  
 KOSHA - Korea Occupational Safety and Health Agency  
 LTV - Long Term Value  
 NIOSH - National Institute for Occupational Safety and Health  
 OSHA - Occupational Safety & Health Administration  
 PBT - Persistent, Bioaccumulative and Toxic  
 PNEC - Predicted No Effect Concentration  
 RID - Regulation concerning the International Carriage of Dangerous Goods by Rail  
 STV - Short Term Value  
 SVHC - Substances of Very High Concern  
 vPvB - very Persistent, very Bioaccumulative

#### Key literature references and sources for data

This Safety Data Sheet has been prepared based on information available for public as TOXNET information, European Chemicals Agency (ECHA) substance dossier, papers from international cancer research institutes (IARC Monographs), U.S. National Toxicology Program data, U.S. Agency for Toxic Substances and Disease Control (ATSDR), PubChem websites and SDS from our raw material manufacturers.

**Revision date**

29.08.2022

**Version**

7.2

**Print date**

29.08.2022

**Additional information**

Indication of changes

Section 8: Update of DNEL and/or PNEC data

If you need an explanation of the change, contact the supplier (SDS@avantorsciences.com).

*The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.*