

# Safety Data Sheet

Revision date: 29.08.2022

Version: 7.3

Print date: 29.08.2022

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

|                                |   |
|--------------------------------|---|
| Trade name/designation:        | Potassium permanganate 30 g/l in orthophosphoric acid Reag. Ph. Eur.<br>1070901 |
| Product No.:                   | 87918   |
| CAS No.:                       | not applicable  |
| Other means of identification: | none  |

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

|                           |                          |
|---------------------------|--------------------------|
| Relevant identified uses: | General chemical reagent |
|---------------------------|--------------------------|

### 1.3 Details of the supplier of the safety data sheet

*Singapore*

#### **VWR Singapore Pte Ltd.**

|                           |                         |
|---------------------------|-------------------------|
| Street                    | 18 Gul Drive            |
| Postal code/City          | Singapore 629468        |
| Telephone                 | +65 6505 0760           |
| Telefax                   | +65 6264 3780           |
| E-mail (competent person) | SDS@avantorsciences.com |

### 1.4 Emergency phone number

|           |   |
|-----------|---|
| Telephone | +65 (0) 6505 0760 (office hours: 8 am-5 pm) |
|-----------|---|

## SECTION 2: Hazard identification

### 2.1 Classification of the substance or mixture

| Hazard classes and hazard categories                      | Hazard statements |
|---|-------------------|
| Substance or mixture corrosive to metals, category 1      | H290              |
| Skin irritation, category 2                               | H315              |
| Eye irritation, category 2                                | H319              |
| Hazardous to the aquatic environment, chronic, category 2 | H411              |
| Reproductive toxicity, category 2                         | H361d             |

### 2.2 Label elements

Hazard pictograms



Signal word: Warning

| Hazard statements |  |
|-------------------|--|
| H290              | May be corrosive to metals.                      |
| H315              | Causes skin irritation.                          |
| H319              | Causes serious eye irritation.                   |
| H361d             | Suspected of damaging the unborn child.          |
| H411              | Toxic to aquatic life with long lasting effects. |

| Precautionary statements |  |
|--------------------------|--|
| P201                     | Obtain special instructions before use.  |
| P280                     | Wear protective gloves/protective clothing/eye protection/face protection.   |
| P264                     | Wash ... thoroughly after handling.  |
| P273                     | Avoid release to the environment.  |
| P234                     | Keep only in original container.   |
| P202                     | Do not handle until all safety precautions have been read and understood.  |
| P302+P352                | IF ON SKIN: Wash with plenty of water/...  |
| P362+P364                | Take off contaminated clothing and wash it before reuse.   |
| P305+P351+P338           | IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. |
| P308+P313                | IF exposed or concerned: Get medical advice/attention.   |
| P321                     | Specific treatment (see ... on this label).  |
| P332+P313                | If skin irritation occurs: Get medical advice/attention.   |
| P337+P313                | If eye irritation persists: Get medical advice/attention.  |
| P390                     | Absorb spillage to prevent material damage.  |
| P391                     | Collect spillage.  |
| P405                     | Store locked up.   |
| P406                     | Store in a corrosive resistant/... container with a resistant inner liner.   |
| P501                     | Dispose of contents/container to ...   |

## 2.3 Other hazards

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

## SECTION 3: Composition / information on ingredients

### 3.1 Substances

not applicable

### 3.2 Mixtures

#### Composition / Information on ingredients

| Substance name         | Concentration | Identifier         | Hazard classes and hazard categories   |
|------------------------|---------------|--------------------|--|
| Potassium permanganate | 2 - 5%        | CAS No.: 7722-64-7 | Ox. Sol. 2 - H272<br>Acute Tox. 4 - H302<br>Skin Corr. 1C - H314<br>Eye Dam. 1 - H318<br>STOT RE 2 - H373<br>Aquatic Acute 1 - H400<br>Aquatic Chronic 1 - H410<br>Repr. 2 - H361d |
| Orthophosphoric acid   | 15 - 25%      | CAS No.: 7664-38-2 | Met. Corr. 1 - H290<br>Acute Tox. 4 - H302<br>Skin Corr. 1B - H314<br>Eye Dam. 1 - H318  |

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

#### General information

If exposed or if you feel unwell: Call a POISON CENTRE or doctor/physician. If unconscious but breathing normally, place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

#### After inhalation

Call a POISON CENTRE/doctor. Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

#### In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

#### After eye contact:

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

#### In case of ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

#### Self-protection of the first aider

First aider: Pay attention to self-protection!

### 4.2 Most important symptoms and effects, both acute and delayed

no data available

### 4.3 Indication of any immediate medical attention and special treatment needed

no data available

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### Suitable extinguishing media

The product itself does not burn.  
Co-ordinate fire-fighting measures to the fire surroundings.

#### Extinguishing media which must not be used for safety reasons

no restriction

### 5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated:  
Pyrolysis products, toxic

### 5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives.  
Special protective equipment for firefighters:

Wear a self-contained breathing apparatus and chemical protective clothing.

#### **Additional information**

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use water spray jet to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

## **SECTION 6: Accidental release measures**

### **6.1 Personal precautions, protective equipment and emergency procedures**

In case of major fire and large quantities: Remove persons to safety.

### **6.2 Environmental precautions**

Discharge into the environment must be avoided.

### **6.3 Methods and material for containment and cleaning up**

Spilled product must never be returned to the original container for recycling. Collect in closed and suitable containers for disposal.

### **6.4 Additional information**

Clear spills immediately.

## **SECTION 7: Handling and storage**

### **7.1 Precautions for safe handling**

All work processes must always be designed so that the following is as low as possible:

Inhalation

skin contact

Eye contact

Use extractor hood (laboratory).

If handled uncovered, arrangements with local exhaust ventilation have to be used.

If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

### **7.2 Conditions for safe storage, including any incompatibilities**

Recommended storage temperature: no data available

Storage class: no data available

Keep container tightly closed and in a well-ventilated place. Keep/Store only in original container.

### **7.3 Specific end use(s)**

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

## **SECTION 8: Exposure controls/personal protection**

### **8.1 Control parameters**

Does not contain substances above concentration limits fixing an occupational exposure limit.

## 8.2 Exposure controls

### 8.2.1 Appropriate engineering controls

no data available

### 8.2.2 Personal protection equipment

no data available

#### *Eye/face protection*

no data available

Recommendation: no data available

#### *Skin protection*

no data available

#### By short-term hand contact

|                                  |                      |
|----------------------------------|----------------------|
| Suitable material:               | NBR (Nitrile rubber) |
| Thickness of the glove material: | 0,12 mm              |
| Breakthrough time::              | > 480 min            |
| Recommended glove articles:      | VWR 112-0998         |

#### By long-term hand contact

|                                  |                      |
|----------------------------------|----------------------|
| Suitable material:               | NBR (Nitrile rubber) |
| Thickness of the glove material: | 0,38 mm              |
| Breakthrough time::              | > 480 min            |
| Recommended glove articles:      | VWR 112-1381         |

#### *Respiratory protection*

no data available

|  |                   |
|--|-------------------|
| Suitable respiratory protection apparatus: | no data available |
| Recommendation:                            | no data available |
| Suitable material:                         | no data available |
| Recommendation:                            | no data available |

#### *Additional information*

no data available

### 8.2.3 Environmental exposure controls

no data available

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

|                      |                   |
|----------------------|-------------------|
| (a) Appearance       |                   |
| Physical state:      | liquid            |
| Colour:              | no data available |
| (b) Odour:           | characteristic    |
| (c) Odour threshold: | no data available |

#### Safety relevant basic data

|  |                           |
|--|---------------------------|
| (d) pH:                                      | no data available         |
| (e) Melting point/freezing point:            | no data available         |
| (f) Initial boiling point and boiling range: | no data available         |
| (g) Flash point:                             | no data available         |
| (h) Evaporation rate:                        | no data available         |
| (i) Flammability (solid, gas):               | not applicable            |
| (j) Flammability or explosive limits         |                           |
| Lower explosion limit:                       | no data available         |
| Upper explosion limit:                       | no data available         |
| (k) Vapour pressure:                         | no data available         |
| (l) Vapour density:                          | no data available         |
| (m) Density:                                 | no data available         |
| (n) Solubility(ies)                          |                           |
| Water solubility:                            | unsoluble (20°C)          |
| (o) Partition coefficient: n-octanol/water:  | no data available         |
| (p) Auto-ignition temperature:               | no data available         |
| (q) Decomposition temperature:               | not applicable            |
| (r) Viscosity                                |                           |
| Kinematic viscosity:                         | no data available         |
| Dynamic viscosity:                           | no data available         |
| (s) Explosive properties:                    | not applicable            |
| (t) Oxidising properties:                    | not applicable            |
| (u) Particle characteristics:                | does not apply to liquids |

### 9.2 Other information

|                        |                   |
|------------------------|-------------------|
| Bulk density:          | no data available |
| Refraction index:      | no data available |
| Dissociation constant: | no data available |
| Surface tension:       | no data available |
| Henry's Law Constant:  | no data available |

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

## 10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

## 10.3 Possibility of hazardous reactions

no data available

## 10.4 Conditions to avoid

no data available

## 10.5 Incompatible materials

no data available

## 10.6 Hazardous decomposition products

no data available

## 10.7 Additional information

no data available

# SECTION 11: Toxicological information

## 11.1 Information on toxicological effects

### Acute effects

#### *Acute oral toxicity:*

Potassium permanganate - LD50: 2000 mg/kg - Rat - (IUCLID)

Potassium permanganate - LDLo: > 100 mg/kg - Human - (IUCLID)

Orthophosphoric acid - LD50: 300 - 2000 mg/kg - Rat - (OECD 423)

#### *Acute dermal toxicity:*

Potassium permanganate - LD50: 2000 mg/kg - Rat - (IUCLID)

#### *Acute inhalation toxicity:*

no data available

### Irritant and corrosive effects

#### *Primary irritation to the skin:*

Causes skin irritation.

#### *Irritation to eyes:*

Causes serious eye irritation.

#### *Irritation to respiratory tract:*

not applicable



**Respiratory or skin sensitisation**

In case of skin contact: not sensitising

After inhalation: not sensitising

**STOT-single exposure**

not applicable

**STOT-repeated exposure**

not applicable

**CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)****Carcinogenicity**

No indication of human carcinogenicity.

**Germ cell mutagenicity**

No indications of human germ cell mutagenicity exist.

**Reproductive toxicity**

Suspected of damaging the unborn child.

**Aspiration hazard**

not applicable

**Other adverse effects**

no data available

**Additional information**

no data available

## SECTION 12: Ecological information

### 12.1 Ecotoxicity

**Fish toxicity:**

Potassium permanganate - LC50: 0.47 mg/l (96 h) *Poecilia reticulata* - IUCLID

**Daphnia toxicity:**

Potassium permanganate - EC50: 0.08 mg/l (48 h) - Office of Pesticide Programs 2000. Pesticide Ecotoxicity Database (Formerly: Environmental Effects Database (EEDB)). Environmental Fate and Effects Division, U.S.EPA, Washington, D.C.

Orthophosphoric acid - EC50: 100 mg/l (48 h) *Daphnia Magna* - OECD 202

**Algae toxicity:**

Potassium permanganate - EC50: 0.45 mg/l (72 h) - Paixao, S.M., L. Silva, A. Fernandez, K. O'Rourke, E. Mendonca, and A. Picado 2008. Performance of a Miniaturized Algal Bioassay in Phytotoxicity Screening. *Ecotoxicology* 17(3):165-171

Orthophosphoric acid - EC10: 100 mg/l (72 h) *Desmodesmus subspicatus* - OECD 201

Orthophosphoric acid - EC50: 100 mg/l (72 h) *Desmodesmus subspicatus* - OECD 201

**Bacteria toxicity:**

Orthophosphoric acid - NOEC: 1000 mg/l (3 h) - OECD 209

## 12.2 Persistence and degradability

no data available

## 12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data available

## 12.4 Mobility in soil:

no data available

## 12.5 Results of PBT/vPvB assessment

not applicable

## 12.6 Other adverse effects

no data available

# SECTION 13: Disposal considerations

## 13.1 Waste treatment methods

### Appropriate disposal / Product

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

### Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

### Additional information

no data available

# SECTION 14: Transport information

## Land transport (ADR/RID)

|      |  |  |
|------|--|--|
| 14.1 | UN-No.:                                    | 1805   |
| 14.2 | Proper Shipping Name:                      | PHOSPHORIC ACID, SOLUTION                          |
| 14.3 | Class(es):                                 | 8  |
|      | Classification code:                       | C1   |
|      | Hazard label(s):                           | 8  |
| 14.4 | Packing group:                             | III  |
| 14.5 | Environmental hazards:                     | Dangerous for the environment                      |
| 14.6 | Special precautions for user:              |  |
|      | Hazard identification number (Kemler No.): | 80   |
|      | tunnel restriction code:                   | E  |
|      |  | (Passage forbidden through tunnels of category E.) |

## Sea transport (IMDG)

|      |         |      |
|------|---------|------|
| 14.1 | UN-No.: | 1805 |
|------|---------|------|

|      |  |                               |
|------|--|-------------------------------|
| 14.2 | Proper Shipping Name:  | PHOSPHORIC ACID SOLUTION      |
| 14.3 | Class(es):   | 8                             |
|      | Classification code:   |                               |
|      | Hazard label(s):   | 8                             |
| 14.4 | Packing group:   | III                           |
| 14.5 | Environmental hazards:   | Dangerous for the environment |
|      | Marine pollutant:  | Yes (P)                       |
| 14.6 | Special precautions for user:  |                               |
|      | Segregation group:   | 1                             |
|      | EmS-No.  | F-A S-B                       |
| 14.7 | Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code |                               |
|      | not relevant   |                               |

#### **Air transport (ICAO-TI / IATA-DGR)**

|      |                               |                          |
|------|-------------------------------|--------------------------|
| 14.1 | UN-No.:                       | 1805                     |
| 14.2 | Proper Shipping Name:         | PHOSPHORIC ACID SOLUTION |
| 14.3 | Class(es):                    | 8                        |
|      | Classification code:          |                          |
|      | Hazard label(s):              | 8                        |
| 14.4 | Packing group:                | III                      |
| 14.5 | Special precautions for user: |                          |

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### National regulations

- Workplace Safety and Health Act
- Workplace Safety and Health (Permissible Exposure Levels of Toxic Substances) Order
- Environmental Protection and Management Act (EPMA) - Second Schedule, Part 1, Control of Hazardous Substances
- Maritime and Port Authority of Singapore (MPA) - Dangerous Goods, Petroleum and Explosives Regulations

## SECTION 16: Other information

#### Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists  
ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road  
AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)  
CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures  
DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)  
DNEL - Derived No Effect Level  
Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)  
IATA-DGR - International Air Transport Association-Dangerous Goods Regulations  
ICAO-TI - International Civil Aviation Organization-Technical Instructions  
IMDG - International Maritime Code for Dangerous Goods  
KOSHA - Korea Occupational Safety and Health Agency  
LTV - Long Term Value  
NIOSH - National Institute for Occupational Safety and Health  
OSHA - Occupational Safety & Health Administration  
PBT - Persistent, Bioaccumulative and Toxic  
PNEC - Predicted No Effect Concentration  
RID - Regulation concerning the International Carriage of Dangerous Goods by Rail  
STV - Short Term Value  
SVHC - Substances of Very High Concern  
vPvB - very Persistent, very Bioaccumulative

#### Key literature references and sources for data

This Safety Data Sheet has been prepared based on information available for public as TOXNET information, European Chemicals Agency (ECHA) substance dossier, papers from international cancer research institutes (IARC Monographs), U.S. National Toxicology Program data, U.S. Agency for Toxic Substances and Disease Control (ATSDR), PubChem websites and SDS from our raw material manufacturers.

**Revision date**

29.08.2022

**Version**

7.3

**Print date**

29.08.2022

**Additional information**

Indication of changes

Section 8: Update of DNEL and/or PNEC data

If you need an explanation of the change, contact the supplier (SDS@avantorsciences.com).

*The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.*