

# Safety Data Sheet according to Regulation (EC) No. 1907/2006 (REACH)

Revision Date: 24-oct-2012

Version No.: 3

## 1. Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

Trade name/designation	Potassium peroxodisulphate ACS
Product No.	0363 (Amresco)
Substance name	Potassium peroxodisulphate
CAS No.	7727-21-1
INDEX no.	016-061-00-1
REACH registration No.	Not yet communicated down the supply chain.
other means of identification	Dipotassium peroxodisulphate Peroxydisulphuric acid dipotassium salt Potassium persulphate di-Potassium peroxodisulphate

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses for laboratory use and chemical production.

### 1.3 Details of the supplier of the safety data sheet

Supplier (manufacturer/importer/only representative/downstream user/distributor)

VWR Singapore Pte Ltd.

Street	18 Gul Drive
Postal code/city	Singapore 629468
country	Singapore
Telephone	+65 6505 0760
Telefax	+65 6264 3780
E-mail (competent person)	vwsds@eu.vwr.com

### 1.4 Emergency telephone

Telephone +65 6505 0760 (office hours: 8 am-5 pm)

## 2. Hazards identification

### 2.1 Classification of the substance or mixture

#### 2.1.1 Classification according to Regulation (EC) No. 1272/2008 [CLP]

hazard classes and hazard categories	Hazard Statements	classification procedure	remark
Oxidising solid, category 3	H272		

Acute toxicity, category 4, oral	H302		
Eye irritation, category 2	H319		
Specific target organ toxicity (single exposure), category 3, vascular	H335		
Skin irritation, category 2	H315		
Respiratory sensitization, category 1	H334		
Skin sensitization, category 1	H317		

## 2.1.2 Classification according to Directive 67/548/EEC or 1999/45/EC

Hazard symbols:	R-phrases
O	R8
Xn	R22
Xi	R36/37/38
Xn	R42/43

## 2.2 Label elements

### 2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]



Signal word

Danger

#### Hazard Statements

H272	May intensify fire; oxidiser.
H302	Harmful if swallowed.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
H315	Causes skin irritation.
H334	May cause allergy or asthma symptoms or breathing difficulties if inhaled.
H317	May cause an allergic skin reaction.

#### Precautionary statements

P210	Keep away from heat/sparks/open flames/hot surfaces. No smoking.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P285	In case of inadequate ventilation wear respiratory protection.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P304+P340	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P309+P311	IF exposed or if you feel unwell: Call a POISON CENTER or doctor/physician.

### 2.2.2 Labelling (67/548/EEC or 1999/45/EC)

Hazard symbols:

O, Xn

#### R-phrases

R8	Contact with combustible material may cause fire.
R22	Harmful if swallowed.
R36/37/38	Irritating to eyes, respiratory system and skin.
R42/43	May cause sensitisation by inhalation and skin contact.

#### S-phrases

S22	Do not breathe dust.
S24	Avoid contact with skin.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S37	Wear suitable gloves.

### 2.3 Other hazards

SVHC

No

---

### 3. Composition/ Information on ingredients

Molecular formula	K2O8S2
Molecular weight (g/mol)	270.32 g/mol
CAS No.	7727-21-1
EC No	231-781-8
INDEX no.	016-061-00-1

---

### 4. First-aid measures

#### 4.1 General information

IF exposed or if you feel unwell: Call a POISON CENTER or doctor/physician. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

#### 4.2 After inhalation

Call a POISON CENTER or doctor/physician. Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

#### 4.3 In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

#### 4.4 After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

#### 4.5 After ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do not induce vomiting. Give nothing to eat or drink.

#### 4.6 Self-protection of the first aider

First aider: Pay attention to self-protection!

#### 4.7 Information to physician:

Symptoms	No data available
Hazards	No data available
Treatment	No data available

---

### 5. Firefighting measures

#### 5.1 Suitable extinguishing media

The product itself does not burn. May intensify fire; oxidiser. Co-ordinate fire-fighting measures to the fire surroundings.

#### 5.2 Extinguishing media which must not be used for safety reasons:

no restriction

#### 5.3 Special hazards arising from the substance or mixture

In case of fire may be liberated: Sulphur oxides

#### 5.4 Advice for firefighters

DO NOT fight fire when fire reaches explosives. In case of fire: Wear self-contained breathing apparatus.

#### 5.5 Additional information

Do not allow run-off from fire-fighting to enter drains or water courses. Do not inhale explosion and combustion gases. Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen. Use water spray jet to protect personnel and to cool endangered containers.

---

### 6. Accidental release measures

#### 6.1 Personal precautions, protective equipment and emergency procedures

Avoid generation of dust. Do not breathe dust. Provide adequate ventilation. Use personal protection equipment. In case of major fire and large quantities: Remove persons to safety.

#### 6.2 Environmental precautions

Do not allow to enter into surface water or drains.

#### 6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Take up dust-free and set down dust-free. Collect in closed and suitable containers for disposal.

## 6.4 Additional information

Clear spills immediately.

---

## 7. Handling and storage

### 7.1 Precautions for safe handling

All work processes must always be designed so that the following is as low as possible: Inhalation. skin contact eye contact. If handled uncovered, arrangements with local exhaust ventilation have to be used. If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means. Keep away from sources of ignition. - No smoking. Usual measures for fire prevention. Protect from moisture.

### 7.2 Conditions for safe storage, including any incompatibilities

storage temperature	15-25°C
---------------------	---------

Keep container tightly closed in a cool, well-ventilated place.

### 7.3 Specific end use(s)

No data available

---

## 8. Exposure controls / Personal protection

### 8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

### 8.2 Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

### 8.3 Personal protective equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn.

#### 8.3.1 Eye / face protection

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

#### 8.3.2 Skin protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms: DIN EN 374 In the case of wanting to use the gloves again,

clean them before taking off and air them well.

By short-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material	0,12 mm
Breakthrough time (maximum wearing time)	>480 min
Recommended glove articles	VWR 112-0998

By long-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material	0,38 mm
Breakthrough time (maximum wearing time)	>480 min
Recommended glove articles	VWR 112-3717 / 112-1381

### 8.3.3 Protective clothing

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

### 8.3.4 Respiratory protection

Respiratory protection necessary at: aerosol or mist formation

Suitable respiratory protection apparatus:	Filtering Half-face mask (DIN EN 149)
Recommendation	VWR 111-0451
Suitable material:	P3
Recommendation	No data available

### 8.4 Additional information

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

---

## 9. Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

#### (a) Appearance

Physical state	solid
Colour	white

#### (b) Odour

No data available

#### (c) Odour threshold

No data available

### Safety relevant basic data

#### (d) pH

No data available

#### (e) Melting point/freezing point

100°C

#### (f) Initial boiling point and boiling range

No data available

#### (g) Flash point

No data available

#### (h) Evaporation rate

No data available

#### (i) Flammability (solid, gas)

not applicable

(j) Upper/lower flammability or explosive limits	
Lower explosion limit (Vol-%)	No data available
Upper explosion limit (Vol-%)	No data available
(k) Vapour pressure	No data available
(l) Vapour density	No data available
(m) Relative density	2.477 g/cm <sup>3</sup> (20°C)
(n) Solubility(ies)	
Water solubility (g/l)	52 g/l (20°C)
at °C:	20
Soluble (g/l) in	No data available
(o) Partition coefficient: n-octanol/water	No data available
(p) Auto-ignition temperature	No data available
(q) Decomposition temperature	No data available
(r) Viscosity	
Kinematic viscosity	No data available
Dynamic viscosity	No data available
(s) Explosive properties	not applicable
(t) Oxidising properties	May intensify fire; oxidiser.

## 9.2 Other information

Bulk density	No data available
refraction index	No data available
dissociation constant	No data available
Surface tension	No data available
Henry constant	No data available

---

## 10. Stability and reactivity

### 10.1 Reactivity

No data available

### 10.2 Chemical stability

No data available

### 10.3 Possibility of hazardous reactions

No data available

### 10.4 Conditions to avoid

No data available

### 10.5 Incompatible materials

No data available

### 10.6 Hazardous decomposition products

No data available

## 10.7 Additional information

No data available

---

## 11. Toxicological information

### 11.1 Information on toxicological effects

#### Acute effects

Acute oral toxicity

Effective dose LD50: 802 mg/kg

species: rat

Exposure time

remark

source RTECS

Acute dermal toxicity

Effective dose No data available

species: No data available

Exposure time

remark

source

Acute inhalation toxicity

Effective dose No data available

species: No data available

Exposure time

remark

source

#### Irritant and corrosive effects

Primary irritation to the skin

Exposure time

species:

Result

Irritation to eyes

Exposure time

species:

Result

Irritation to respiratory tract

Exposure time

species:

Result

#### Sensitisation

In case of skin contact No data available



After inhalation

No data available

**Specific target organ toxicity (single exposure)**

May cause respiratory irritation.

**Specific target organ toxicity (repeated exposure)**

not relevant

**CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**

**Carcinogenicity**

No indication of human carcinogenicity.

**Germ cell mutagenicity/Genotoxicity**

No indications of human germ cell mutagenicity exist.

**Reproductive toxicity**

No indications of human reproductive toxicity exist.

**Aspiration hazard**

not relevant

11.2 Other adverse effects

No data available

11.3 Additional information

No data available

---

12. Ecological information

12.1 Ecotoxicity

**Acute (short-term) fish toxicity**

LC50: No data available

EC50

species:

Exposure time

**Chronic (long-term) fish toxicity**

LC50: No data available

EC50

species:  
Exposure time

**Acute (short-term) daphnia toxicity**

LC50: No data available  
EC50  
species:  
Exposure time

**Chronic (long-term) daphnia toxicity**

LC50: No data available  
EC50  
species:  
Exposure time

**Acute (short-term) algae toxicity**

LC50: No data available  
EC50  
species:  
Exposure time

**Chronic (long-term) algae toxicity**

LC50: No data available  
EC50  
species:  
Exposure time

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT assessment

No data available

12.6 Other adverse effects

No data available

---

13. Disposal considerations

13.1 Waste treatment methods

**Appropriate disposal / Product**

Dispose according to legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product

No data available

### **Appropriate disposal / Package**

#### 13.2 Additional information

No data available

---

#### 14. Transport information

##### 14.1 Land transport (ADR/RID)

UN-No.	1492
Proper Shipping Name	POTASSIUM PERSULPHATE
Class(es)	5.1
Classification code:	O2
Packing group	III
Hazard label(s)	5.1

##### 14.2 Sea transport (IMDG)

UN-No.	1492
Proper Shipping Name	POTASSIUM PERSULPHATE
Class(es)	5.1
Classification code:	O2
Packing group	III
Marine pollutant	
Segregation group	

##### 14.3 Air transport (ICAO-TI / IATA-DGR)

UN-No.	1492
Proper Shipping Name	POTASSIUM PERSULPHATE
Class(es)	5.1
Classification code:	O2
Packing group	III

##### 14.4 Additional information

No data available

---

#### 15. Regulatory information

##### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

## 15.2 Chemical Safety Assessment

No data available

## 16. Other information

## 16.1 Relevant R-, H- and EUH-phrases (Number and full text)

R8	Contact with combustible material may cause fire.
R22	Harmful if swallowed.
R36/37/38	Irritating to eyes, respiratory system and skin.
R42/43	May cause sensitisation by inhalation and skin contact.

H272	May intensify fire; oxidiser.
H302	Harmful if swallowed.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
H315	Causes skin irritation.
H334	May cause allergy or asthma symptoms or breathing difficulties if inhaled.
H317	May cause an allergic skin reaction.

## 16.2 Additional information

Indication of changes

general update

*The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.*