

Safety Data Sheet

Revision date: 29.08.2022

Version: 7.2

Print date: 29.08.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name/designation:	Ninhydrin 0.4% in 1-butanol 95% (v/v) / Acetic acid 5% (v/v)
Product No.:	87879
CAS No.:	not applicable
Other means of identification:	none

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses:	General chemical reagent
---------------------------	--------------------------

1.3 Details of the supplier of the safety data sheet

Singapore

VWR Singapore Pte Ltd.

Street	18 Gul Drive
Postal code/City	Singapore 629468
Telephone	+65 6505 0760
Telefax	+65 6264 3780
E-mail (competent person)	SDS@avantorsciences.com

1.4 Emergency phone number

Telephone	+65 (0) 6505 0760 (office hours: 8 am-5 pm)
-----------	---

SECTION 2: Hazard identification

2.1 Classification of the substance or mixture

Hazard classes and hazard categories	Hazard statements
Flammable liquid, category 3	H226
Acute toxicity, category 4, oral	H302
Skin irritation, category 2	H315
Serious eye damage, category 1	H318
Specific target organ toxicity (single exposure), category 3, Respiratory tract irritation	H335
Specific target organ toxicity (single exposure), category 3, narcotic effect	H336

2.2 Label elements

Hazard pictograms



Signal word: Danger

Hazard statements	
H226	Flammable liquid and vapour.
H302	Harmful if swallowed.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.

Precautionary statements	
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P233	Keep container tightly closed.
P243	Take precautionary measures against static discharge.
P240	Ground/bond container and receiving equipment.
P241	Use explosion-proof electrical/ventilating/lighting/equipment.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P261	Avoid breathing dust/fume/gas/mist/vapours/spray.
P264	Wash ... thoroughly after handling.
P271	Use only outdoors or in a well-ventilated area.
P270	Do not eat, drink or smoke when using this product.
P242	Use only non-sparking tools.
P301+P312	IF SWALLOWED: Call a POISON CENTER/doctor/.../if you feel unwell.
P302+P352	IF ON SKIN: Wash with plenty of water/...
P303+P361+P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
P362+P364	Take off contaminated clothing and wash it before reuse.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310	Immediately call a POISON CENTER/doctor/...
P312	Call a POISON CENTER/doctor/.../if you feel unwell.
P321	Specific treatment (see ... on this label).
P332+P313	If skin irritation occurs: Get medical advice/attention.
P370+P378	In case of fire: Use... to extinguish.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P403+P235	Store in a well-ventilated place. Keep cool.
P405	Store locked up.
P501	Dispose of contents/container to ...

2.3 Other hazards

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

SECTION 3: Composition / information on ingredients

3.1 Substances

not applicable

3.2 Mixtures

Composition / Information on ingredients

Substance name	Concentration	Identifier	Hazard classes and hazard categories
Ninhydrin hydrate	< 1%	CAS No.: 485-47-2	Acute Tox. 4 - H302 Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 STOT SE 3 - H335
Acetic acid	5 - 10%	CAS No.: 64-19-7	Flam. Liq. 3 - H226 Skin Corr. 1A - H314
Butan-1-ol	> 90%	CAS No.: 71-36-3	Flam. Liq. 3 - H226 Acute Tox. 4 - H302 Skin Irrit. 2 - H315 Eye Dam. 1 - H318 STOT SE 3 - H335 STOT SE 3 - H336

SECTION 4: First aid measures

4.1 Description of first aid measures

General information

IF exposed: Immediately call a POISON CENTRE/doctor. If unconscious but breathing normally, place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

After inhalation

Immediately call a POISON CENTRE/doctor. Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

After eye contact:

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

In case of ingestion

Immediately call a POISON CENTRE/doctor. Do NOT induce vomiting. Rinse mouth thoroughly with water. Give nothing to eat or drink.

Self-protection of the first aider

First aider: Pay attention to self-protection!

4.2 Most important symptoms and effects, both acute and delayed

no data available

4.3 Indication of any immediate medical attention and special treatment needed

no data available

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Water spray
ABC-powder
Carbon dioxide (CO₂)
Nitrogen

Extinguishing media which must not be used for safety reasons

no restriction

5.2 Special hazards arising from the substance or mixture

In case of fire may be liberated:

Pyrolysis products, toxic

5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives.

Special protective equipment for firefighters:

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen.

Use water spray jet to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety.

6.2 Environmental precautions

Discharge into the environment must be avoided.

6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Collect in closed and suitable containers for disposal.

6.4 Additional information

Clear spills immediately.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

All work processes must always be designed so that the following is as low as possible:

Inhalation

skin contact

Eye contact

Use extractor hood (laboratory).

If handled uncovered, arrangements with local exhaust ventilation have to be used.

If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: no data available

Storage class: no data available

Keep container tightly closed and in a well-ventilated place. Keep/Store only in original container.

7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredient (Designation)	Regulatory information	Country	Limit value type (country of origin)	Limit value	Remark
Acetic acid	Workplace Safety and Health (General Provisions) Regulations, WORKPLACE SAFETY AND HEALTH ACT (CHAPTER 354A, SECTION 65)	SG	LTV	10 ppm - 25 mg/m ³	
Acetic acid	Workplace Safety and Health (General Provisions) Regulations, WORKPLACE SAFETY AND HEALTH ACT (CHAPTER 354A, SECTION 65)	SG	STV	15 ppm - 37 mg/m ³	

8.2 Exposure controls

8.2.1 Appropriate engineering controls

no data available

8.2.2 Personal protection equipment

no data available

Eye/face protection

no data available

Recommendation: no data available

Skin protection

Wear suitable gloves. When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. In the case of wanting to use the gloves again, clean them before taking off and air them well. Check leak tightness/impermeability prior to use.

By short-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,12 mm
Breakthrough time::	70 min
Recommended glove articles:	VWR 112-0998

By long-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,38 mm
Breakthrough time::	> 480 min
Recommended glove articles:	VWR 112-1381

Respiratory protection

no data available

Suitable respiratory protection apparatus:	no data available
Recommendation:	no data available
Suitable material:	no data available
Recommendation:	no data available

Additional information

no data available

8.2.3 Environmental exposure controls

no data available

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	liquid
Colour:	no data available
(b) Odour:	no data available
(c) Odour threshold:	no data available

Safety relevant basic data

(d) pH:	no data available
(e) Melting point/freezing point:	no data available
(f) Initial boiling point and boiling range:	no data available
(g) Flash point:	no data available
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	Flammable liquid and vapour.
(j) Flammability or explosive limits	
Lower explosion limit:	no data available
Upper explosion limit:	no data available
(k) Vapour pressure:	no data available
(l) Vapour density:	no data available
(m) Density:	no data available
(n) Solubility(ies)	
Water solubility:	no data available
(o) Partition coefficient: n-octanol/water:	no data available
(p) Auto-ignition temperature:	no data available
(q) Decomposition temperature:	not applicable
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	no data available
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable
(u) Particle characteristics:	does not apply to liquids

9.2 Other information

Bulk density:	no data available
Refraction index:	no data available
Dissociation constant:	no data available
Surface tension:	no data available
Henry's Law Constant:	no data available

SECTION 10: Stability and reactivity

10.1 Reactivity

no data available

10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

no data available

10.6 Hazardous decomposition products

no data available

10.7 Additional information

no data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:

Ninhydrin hydrate - LD50: > 600 mg/kg - Rat - (Merck KGaA)

Acetic acid - LD50: > 3310 mg/kg - Rat - (RTECS)

Butan-1-ol - LD50: > 790 mg/kg - Rat - (RTECS)

Acute dermal toxicity:

Acetic acid - LD50: > 1060 mg/kg - Rabbit - (IUCLID)

Butan-1-ol - LD50: > 3400 mg/kg - Rabbit - (RTECS)

Acute inhalation toxicity:

Acetic acid - LC50: 11.4 mg/l - Rat - (National Library of Medicine ChemID Plus (NLM CIP))

Butan-1-ol - LC50: > 8000 ppm - Rat - (Japan GHS Basis for Classification Data)

Irritant and corrosive effects

Primary irritation to the skin:

Causes skin irritation.

Irritation to eyes:

Causes serious eye damage.

Irritation to respiratory tract:

May cause respiratory irritation.

Respiratory or skin sensitisation

In case of skin contact: not sensitising

After inhalation: not sensitising

STOT-single exposure

May cause drowsiness or dizziness.

STOT-repeated exposure

not applicable

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**Carcinogenicity**

No indication of human carcinogenicity.

Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.

Reproductive toxicity

No indications of human reproductive toxicity exist.

Aspiration hazard

not applicable

Other adverse effects

no data available

Additional information

no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Fish toxicity:

Acetic acid - LC50: mg/l (96 h) Oncorhynchus mykiss - OECD 203

Butan-1-ol - LC50: 1376 mg/l (96 h) Pimephales promelas - OECD 203

Daphnia toxicity:

Acetic acid - LC50: 65 mg/l (48 h) - Janssen, C.R., E.Q. Espiritu, and G. Persoone 1993. Evaluation of the new ""Enzymatic Inhibition"" Criterion for Rapid Toxicity Testing with Daphnia magna

Acetic acid - EC50: mg/l (48 h) Daphnia magna - OECD 202

Butan-1-ol - NOEC: 1.1 mg/l (21 d) Daphnia magna - OECD 211

Butan-1-ol - EC50: 1328 mg/l (48 h) Daphnia magna - OECD 202

Algae toxicity:

Acetic acid - EC50: mg/l (72 h) - ISO 10253

Butan-1-ol - EC50: 225 mg/l (96 h) Pseudokirchneriella subcapitata - OECD 201

Bacteria toxicity:

Butan-1-ol - EC10: 2476 mg/l (17 h) *Pseudomonas putida* - DIN 38412

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data available

12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

not applicable

12.6 Other adverse effects

no data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods
Appropriate disposal / Product

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

Appropriate disposal / Package

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

Additional information

no data available

SECTION 14: Transport information

Land transport (ADR/RID)

14.1	UN-No.:	1993
14.2	Proper Shipping Name:	FLAMMABLE LIQUID, N.O.S. (BUTANOL / ACETIC ACID)
14.3	Class(es):	3
	Classification code:	F1
	Hazard label(s):	3
14.4	Packing group:	III
14.5	Environmental hazards:	No
14.6	Special precautions for user:	
	Hazard identification number (Kemler No.):	
	tunnel restriction code:	E
		(Passage forbidden through tunnels of category E.)

Sea transport (IMDG)

14.1	UN-No.:	1993
14.2	Proper Shipping Name:	FLAMMABLE LIQUID, N.O.S. (BUTANOL / ACETIC ACID)
14.3	Class(es):	3
	Classification code:	
	Hazard label(s):	3
14.4	Packing group:	III
14.5	Environmental hazards:	No
	Marine pollutant:	No
14.6	Special precautions for user:	
	Segregation group:	-
	EmS-No.	F-E S-E
14.7	Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	not relevant

Air transport (ICAO-TI / IATA-DGR)

14.1	UN-No.:	1993
14.2	Proper Shipping Name:	FLAMMABLE LIQUID, N.O.S. (BUTANOL / ACETIC ACID)
14.3	Class(es):	3
	Classification code:	
	Hazard label(s):	3
14.4	Packing group:	III
14.5	Special precautions for user:	

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations

- Workplace Safety and Health Act
- Workplace Safety and Health (Permissible Exposure Levels of Toxic Substances) Order
- Environmental Protection and Management Act (EPMA) - Second Schedule, Part 1, Control of Hazardous Substances
- Maritime and Port Authority of Singapore (MPA) - Dangerous Goods, Petroleum and Explosives Regulations

SECTION 16: Other information

Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists
 ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road
 AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)
 CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures
 DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)
 DNEL - Derived No Effect Level
 Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)
 IATA-DGR - International Air Transport Association-Dangerous Goods Regulations
 ICAO-TI - International Civil Aviation Organization-Technical Instructions
 IMDG - International Maritime Code for Dangerous Goods
 KOSHA - Korea Occupational Safety and Health Agency
 LTV - Long Term Value
 NIOSH - National Institute for Occupational Safety and Health
 OSHA - Occupational Safety & Health Administration
 PBT - Persistent, Bioaccumulative and Toxic
 PNEC - Predicted No Effect Concentration
 RID - Regulation concerning the International Carriage of Dangerous Goods by Rail
 STV - Short Term Value
 SVHC - Substances of Very High Concern
 vPvB - very Persistent, very Bioaccumulative

Key literature references and sources for data

This Safety Data Sheet has been prepared based on information available for public as TOXNET information, European Chemicals Agency (ECHA) substance dossier, papers from international cancer research institutes (IARC Monographs), U.S. National Toxicology Program data, U.S. Agency for Toxic Substances and Disease Control (ATSDR), PubChem websites and SDS from our raw material manufacturers.

Revision date

29.08.2022

Version

7.2

Print date

29.08.2022

Additional information

Indication of changes

Section 8: Update of DNEL and/or PNEC data

If you need an explanation of the change, contact the supplier (SDS@avantorsciences.com).

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.