



Material	20067.400
Material description	Acetone
Grade	HiPerSolv CHROMANORM for HPLC
CAS Number	67-64-1
Molecular formula	CH ₃ COCH ₃
Molecular mass	58.08

Characteristics	Specifications
Assay (on anhydrous substance)	Min. 99.8 %
Acidity	Max. 0.0005 meq/g
Alkalinity	Max. 0.0002 meq/g
Evaporation residue	Max. 5 ppm
Water	Max. 0.2 %
Absorbance (345 nm)	Max. 0.3
Absorbance (350 nm)	Max. 0.1
Absorbance (360 nm)	Max. 0.01
Transmittance (345 nm)	Min. 50 %
Transmittance (350 nm)	Min. 80 %
Transmittance (360 nm)	Min. 98 %

Signature

We certify that this batch conforms to the specifications listed above.

This document has been produced electronically and is valid without a signature.

Isabelle Habay, Head of Laboratory - Briare
VWR International S.A.S.; Z.I. de Vaugereau; FR-45250 Briare;
France

For Professional use in Laboratory or Manufacturing. Not for use as an Active Pharmaceutical Ingredient or Food or Animal Feed. Suitability and intended use of the product remains the responsibility of the user.