

# Safety Data Sheet

Revision date: 22.07.2022

Version: 7.1

Print date: 22.07.2022

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

Trade name/designation:	Neutral red (C.I. 50040) Gurr®
Product No.:	34056
CAS No.:	553-24-2
Other means of identification:	Basic Red 5, N8,N8,3-Trimethyl-2,8-phenazinediamine monohydrochloride, Toluylene red

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses:	General chemical reagent
---------------------------	--------------------------

### 1.3 Details of the supplier of the safety data sheet

#### *Singapore*

#### **VWR Singapore Pte Ltd.**

Street	18 Gul Drive
Postal code/City	Singapore 629468
Telephone	+65 6505 0760
Telefax	+65 6264 3780
E-mail (competent person)	SDS@avantorsciences.com

### 1.4 Emergency phone number

Telephone	+65 (0) 6505 0760 (office hours: 8 am-5 pm)
-----------	---

## SECTION 2: Hazard identification

### 2.1 Classification of the substance or mixture

The substance is classified as not hazardous.

### 2.2 Label elements

The product does not have to be labelled.

### 2.3 Other hazards

not applicable

## SECTION 3: Composition / information on ingredients

### 3.1 Substances

Substance name	Neutral red
Molecular formula	C <sub>15</sub> H <sub>17</sub> ClN <sub>4</sub>
Molecular weight	288.78 g/mol
CAS No.	553-24-2

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

#### General information

When in doubt or if symptoms are observed, get medical advice. If unconscious but breathing normally, place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

#### After inhalation

Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration. In case of respiratory tract irritation, consult a physician.

#### In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

#### After eye contact:

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

#### In case of ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

#### Self-protection of the first aider

First aider: Pay attention to self-protection!

### 4.2 Most important symptoms and effects, both acute and delayed

no data available

### 4.3 Indication of any immediate medical attention and special treatment needed

no data available

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### Suitable extinguishing media

The product itself does not burn.

Co-ordinate fire-fighting measures to the fire surroundings.

**Extinguishing media which must not be used for safety reasons**

no restriction

**5.2 Special hazards arising from the substance or mixture**

In case of fire may be liberated:

Carbon monoxide

Carbon dioxide (CO<sub>2</sub>)

Hydrogen chloride (HCl)

Nitrogen oxides (NO<sub>x</sub>)

**5.3 Advice for firefighters**

DO NOT fight fire when fire reaches explosives.

Special protective equipment for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

**Additional information**

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use water spray jet to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

**SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures**

Avoid dust formation.

**6.2 Environmental precautions**

Do not allow to enter into surface water or drains.

**6.3 Methods and material for containment and cleaning up**

Spilled product must never be returned to the original container for recycling. Clean contaminated articles and floor according to the environmental legislation. Collect in closed and suitable containers for disposal.

**6.4 Additional information**

Clear spills immediately.

**SECTION 7: Handling and storage****7.1 Precautions for safe handling**

Avoid:

Inhalation

Avoid contact with eyes and skin.

Use extractor hood (laboratory).

If handled uncovered, arrangements with local exhaust ventilation have to be used.

If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

Protect from moisture.

## 7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: 15-25°C

Storage class: 10-13

Keep container tightly closed and in a well-ventilated place.

## 7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

# SECTION 8: Exposure controls/personal protection

## 8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

## 8.2 Exposure controls

### 8.2.1 Appropriate engineering controls

no data available

### 8.2.2 Personal protection equipment

no data available

#### *Eye/face protection*

no data available

Recommendation: no data available

#### *Skin protection*

no data available

#### By short-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,12 mm
Breakthrough time::	> 480 min
Recommended glove articles:	VWR 112-0998

#### By long-term hand contact

Suitable material:	NBR (Nitrile rubber)
Thickness of the glove material:	0,38 mm
Breakthrough time::	> 480 min
Recommended glove articles:	VWR 112-3717 / 112-1381

#### *Respiratory protection*

no data available

Suitable respiratory protection apparatus:	no data available
Recommendation:	no data available
Suitable material:	no data available
Recommendation:	no data available

#### Additional information

no data available

#### 8.2.3 Environmental exposure controls

no data available

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	solid
Colour:	dark green
(b) Odour:	no data available
(c) Odour threshold:	no data available

#### Safety relevant basic data

(d) pH:	3.1 (10 g/l; H <sub>2</sub> O; 20 °C)
(e) Melting point/freezing point:	290 °C
(f) Initial boiling point and boiling range:	no data available
(g) Flash point:	no data available
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	not applicable
(j) Flammability or explosive limits	
Lower explosion limit:	no data available
Upper explosion limit:	no data available
(k) Vapour pressure:	no data available
(l) Vapour density:	no data available
(m) Density:	no data available
(n) Solubility(ies)	
Water solubility:	50 g/l (25 °C)
(o) Partition coefficient: n-octanol/water:	no data available
(p) Auto-ignition temperature:	no data available
(q) Decomposition temperature:	290 °C (1013 hPa)
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	no data available
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable
(u) Particle characteristics:	not applicable - no nanoform/not combustible

### 9.2 Other information

Bulk density:	no data available
Refraction index:	no data available
Dissociation constant:	no data available
Surface tension:	no data available
Henry's Law Constant:	no data available

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

### 10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature).

### 10.3 Possibility of hazardous reactions

no data available

### 10.4 Conditions to avoid

no data available

### 10.5 Incompatible materials

no data available

### 10.6 Hazardous decomposition products

no data available

### 10.7 Additional information

no data available

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute effects

*Acute oral toxicity:*

no data available

*Acute dermal toxicity:*

no data available

*Acute inhalation toxicity:*

no data available

#### Irritant and corrosive effects

*Primary irritation to the skin:*

not applicable

*Irritation to eyes:*

not applicable

*Irritation to respiratory tract:*

not applicable

**Respiratory or skin sensitisation**

In case of skin contact: not sensitising

After inhalation: not sensitising

**STOT-single exposure**

not applicable

**STOT-repeated exposure**

not applicable

**CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)****Carcinogenicity**

No indication of human carcinogenicity.

**Germ cell mutagenicity**

No indications of human germ cell mutagenicity exist.

**Reproductive toxicity**

No indications of human reproductive toxicity exist.

**Aspiration hazard**

not applicable

**Other adverse effects**

no data available

**Additional information**

no data available

## SECTION 12: Ecological information

### 12.1 Ecotoxicity

**Fish toxicity:**

no data available

**Daphnia toxicity:**

no data available

**Algae toxicity:**

no data available

**Bacteria toxicity:**

no data available

### 12.2 Persistence and degradability

no data available

### 12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data available

**12.4 Mobility in soil:**

no data available

**12.5 Results of PBT/vPvB assessment**

not applicable

**12.6 Other adverse effects**

no data available

**SECTION 13: Disposal considerations****13.1 Waste treatment methods****Appropriate disposal / Product**

Dispose according to local legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

**Appropriate disposal / Package**

Dispose according to local legislation. Handle contaminated packages in the same way as the substance itself.

**Additional information**

no data available

**SECTION 14: Transport information****Land transport (ADR/RID)**

No dangerous good in sense of this transport regulation.

**Sea transport (IMDG)**

No dangerous good in sense of this transport regulation.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code  
not relevant

**Air transport (ICAO-TI / IATA-DGR)**

No dangerous good in sense of this transport regulation.



## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### National regulations

- Workplace Safety and Health Act
- Workplace Safety and Health (Permissible Exposure Levels of Toxic Substances) Order
- Environmental Protection and Management Act (EPMA) - Second Schedule, Part 1, Control of Hazardous Substances
- Maritime and Port Authority of Singapore (MPA) - Dangerous Goods, Petroleum and Explosives Regulations

## SECTION 16: Other information

#### Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists  
 ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road  
 AGS - Committee on Hazardous Substances (Ausschuss für Gefahrstoffe)  
 CLP - Regulation on Classification, Labelling and Packaging of Substances and Mixtures  
 DFG - German Research Foundation (Deutsche Forschungsgemeinschaft)  
 DNEL - Derived No Effect Level  
 Gestis - Information system on hazardous substances of the German Social Accident Insurance (Gefahrstoffinformationssystem der Deutschen Gesetzlichen Unfallversicherung)  
 IATA-DGR - International Air Transport Association-Dangerous Goods Regulations  
 ICAO-TI - International Civil Aviation Organization-Technical Instructions  
 IMDG - International Maritime Code for Dangerous Goods  
 KOSHA - Korea Occupational Safety and Health Agency  
 LTV - Long Term Value  
 NIOSH - National Institute for Occupational Safety and Health  
 OSHA - Occupational Safety & Health Administration  
 PBT - Persistent, Bioaccumulative and Toxic  
 PNEC - Predicted No Effect Concentration  
 RID - Regulation concerning the International Carriage of Dangerous Goods by Rail  
 STV - Short Term Value  
 SVHC - Substances of Very High Concern  
 vPvB - very Persistent, very Bioaccumulative

#### Key literature references and sources for data

This Safety Data Sheet has been prepared based on information available for public as TOXNET information, European Chemicals Agency (ECHA) substance dossier, papers from international cancer research institutes (IARC Monographs), U.S. National Toxicology Program data, U.S. Agency for Toxic Substances and Disease Control (ATSDR), PubChem websites and SDS from our raw material manufacturers.

**Revision date**

22.07.2022

**Version**

7.1

**Print date**

22.07.2022

**Additional information**

## Indication of changes

Section 7.1: Introduction of general occupation hygienic measures  
Section 9: Introduction of particle characteristics  
Section 16: Introduction of key literature references and sources of data

If you need an explanation of the change, contact the supplier (SDS@avantorsciences.com).

*The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.*